

New



A SERCEL BUSINESS UNIT

# IGAUGE5

EXTRA SLIM DOWNHOLE  
MEMORY GAUGE

### ENHANCED RELIABILITY

Low Maintenance gauge operated by anyone in less than 10 mins.  
Laterally locked battery avoids disconnection in operation.  
Metal-to-metal seal for better protection of the electronic board.

### METROLOG BREAKTHROUGH

External communication port reduces maintenance cost and time.  
Smart battery system displays the remaining power of your cells.  
High-temperature electronic board with 4 times redundant memories.

### APPLICATIONS

For accurate reservoir monitoring, static/dynamic gradient and build-up.  
For DST, coil tubing and all slim-hole operations.

### SPECIFICATIONS

PRESSURE		PiezoResistive Sensor
Range	0-1500 up to 0-15000 psi (0-100 to 0-1000 bar)	
Accuracy	± 0.05% FS	
Resolution	<0.05 psi (<0.003 bar)	
TEMPERATURE		PT100
Range	0 to 300 °F (-20 to 150 °C)	
Accuracy	± 0.6 °F (± 0.3 °C)	
Resolution	<0.01 °F (<0.005 °C)	
MECHANICS		
Material	High-Quality Inconel suitable for sour service (H <sub>2</sub> S, CO <sub>2</sub> , acid)	
OD	3/4" (19 mm)	
Length	9" (23 cm)	
Weight	0.5 lbs (250 g)	
Threads	5/8" 11 UNC (pin up x box down)	
Bottom nose	1/4" NPT (female)	
MEMORY		
Capacity	4 200 000 data points of pressure and/or temperature	
COMPUTER AND SOFTWARE		
Programming Modes	Conventional, Advanced	
Parameters	1s-18h Scanning Rate, Time delay, Pressure start (Trigger, Threshold)	
Windows	Compatible with Windows 2000/XP/Vista/7	
Connector	RS232/USB	
BATTERY TYPE		
Z15E/LZ15E	Cumulative operating time up to 200 days.	



**Metrolog**  
Technoparc. Bat.2. Avenue L'occitane. BP 27415. 31674 Labège Cedex France  
**Telephone:** (33) 5 61 34 80 74. **Fax:** (33) 5 61 20 41 31. **E-mail:** sales@metrolog.com  
[www.metrolog.com](http://www.metrolog.com)

**Sercel**  
S.A. au capital de 2 000 000 €. Siège Social: 16 rue de Bel-Air 44470 Carquefou.  
378.040.497 R.C.S. Nantes. Code APE 2651B  
[www.sercel.com](http://www.sercel.com)

Printed in France. © Sercel 09/08 - Information subject to change without notice. TSO\_036\_0

Ahead of the Curve<sup>SM</sup>